



## CONNECTOR SLEEVES



### Technical description



| Code      | A    | B   | C   | D   | E   | F   | G   | Colour                             | Notes     | MOQ-Pcs |
|-----------|------|-----|-----|-----|-----|-----|-----|------------------------------------|-----------|---------|
| 14909CA00 | 15,5 | 2,5 | 5,0 | 2,0 | 5,8 | 0,9 | 2,2 | Trasparente / Transparent          | -         | 1.000   |
| 14910CA00 | 15,5 | 2,5 | 5,0 | 2,5 | 5,8 | 0,9 | 2,2 | Trasparente / Transparent          | -         | 1.000   |
| 14911CA00 | 15,5 | 2,5 | 5,0 | 3,0 | 5,8 | 0,9 | 2,2 | Trasparente / Transparent          | -         | 1.000   |
| 14912CA00 | 15,0 | 3,0 | 5,0 | 3,5 | 5,8 | 0,9 | 2,2 | Trasparente / Transparent          | -         | 1.000   |
| 14913CA00 | 15,0 | 3,0 | 5,0 | 4,0 | 5,8 | 0,9 | 2,2 | Trasparente / Transparent          | -         | 1.000   |
| 14914CA00 | 15,0 | 3,0 | 5,0 | 4,5 | 5,8 | 0,9 | 2,2 | Trasparente / Transparent          | -         | 1.000   |
| 14915CA08 | 15,5 | 2,5 | 5,0 | 2,0 | 5,8 | 0,9 | 2,2 | Blu trasparente / Transparent blue | V0 (UL94) | 1.000   |
| 14916CA08 | 15,5 | 2,5 | 5,0 | 2,5 | 5,8 | 0,9 | 2,2 | Blu trasparente / Transparent blue | V0 (UL94) | 1.000   |
| 14917CA08 | 15,5 | 2,5 | 5,0 | 3,0 | 5,8 | 0,9 | 2,2 | Blu trasparente / Transparent blue | V0 (UL94) | 1.000   |

| Code      | A    | B   | C   | D   | E   | F   | G   | Colour                                | Notes     | MOQ-Pcs |
|-----------|------|-----|-----|-----|-----|-----|-----|---------------------------------------|-----------|---------|
| 14918CA08 | 15,0 | 3,0 | 5,0 | 3,5 | 5,8 | 0,9 | 2,2 | Blu trasparente /<br>Transparent blue | V0 (UL94) | 1.000   |
| 14919CA08 | 15,0 | 3,0 | 5,0 | 4,0 | 5,8 | 0,9 | 2,2 | Blu trasparente /<br>Transparent blue | V0 (UL94) | 1.000   |
| 14920CA08 | 15,0 | 3,0 | 5,0 | 4,5 | 5,8 | 0,9 | 2,2 | Blu trasparente /<br>Transparent blue | V0 (UL94) | 1.000   |
| 14921CA00 | 16,0 | 3,0 | 5,0 | 2,0 | 6,5 | 0,9 | 3,0 | Trasparente /<br>Transparent          | -         | 1.000   |
| 14922CA00 | 16,0 | 3,0 | 5,0 | 2,5 | 6,5 | 0,9 | 3,0 | Trasparente /<br>Transparent          | -         | 1.000   |
| 14923CA00 | 16,0 | 3,0 | 5,0 | 3,0 | 6,5 | 0,9 | 3,0 | Trasparente /<br>Transparent          | -         | 1.000   |
| 14924CA00 | 16,0 | 3,0 | 5,0 | 3,5 | 6,5 | 0,9 | 3,0 | Trasparente /<br>Transparent          | -         | 1.000   |
| 14925CA00 | 16,0 | 3,0 | 5,0 | 4,0 | 6,5 | 0,9 | 3,0 | Trasparente /<br>Transparent          | -         | 1.000   |
| 14926CA08 | 16,0 | 3,0 | 5,0 | 2,0 | 6,5 | 0,9 | 3,0 | Blu trasparente /<br>Transparent blue | V0 (UL94) | 1.000   |
| 14927CA08 | 16,0 | 3,0 | 5,0 | 2,5 | 6,5 | 0,9 | 3,0 | Blu trasparente /<br>Transparent blue | V0 (UL94) | 1.000   |
| 14928CA08 | 16,0 | 3,0 | 5,0 | 3,0 | 6,5 | 0,9 | 3,0 | Blu trasparente /<br>Transparent blue | V0 (UL94) | 1.000   |
| 14929CA08 | 16,0 | 3,0 | 5,0 | 3,5 | 6,5 | 0,9 | 3,0 | Blu trasparente /<br>Transparent blue | V0 (UL94) | 1.000   |
| 14930CA08 | 16,0 | 3,0 | 5,0 | 4,0 | 6,5 | 0,9 | 3,0 | Blu trasparente /<br>Transparent blue | V0 (UL94) | 1.000   |
| 14931CA00 | 16,0 | 3,0 | 5,0 | 2,0 | 8,0 | 1,0 | 3,5 | Trasparente /<br>Transparent          | -         | 1.000   |
| 14932CA00 | 16,0 | 3,0 | 5,0 | 2,5 | 8,0 | 1,0 | 3,5 | Trasparente /<br>Transparent          | -         | 1.000   |
| 14933CA00 | 15,5 | 3,5 | 5,0 | 3,0 | 8,0 | 1,0 | 3,5 | Trasparente /<br>Transparent          | -         | 1.000   |
| 14934CA00 | 16,5 | 2,5 | 5,0 | 3,2 | 8,0 | 1,0 | 3,5 | Trasparente /<br>Transparent          | -         | 1.000   |
| 14935CA00 | 16,0 | 3,0 | 5,0 | 3,5 | 8,0 | 1,0 | 3,5 | Trasparente /<br>Transparent          | -         | 1.000   |
| 14936CA00 | 17,5 | 2,5 | 5,0 | 3,8 | 8,0 | 1,0 | 3,5 | Trasparente /<br>Transparent          | -         | 1.000   |
| 14937CA00 | 16,5 | 3,0 | 5,0 | 4,0 | 8,0 | 1,0 | 3,5 | Trasparente /<br>Transparent          | -         | 1.000   |

| Code      | A    | B   | C   | D   | E   | F   | G   | Colour                             | Notes     | MOQ-Pcs |
|-----------|------|-----|-----|-----|-----|-----|-----|------------------------------------|-----------|---------|
| 14938CA00 | 17,5 | 2,5 | 5,0 | 4,8 | 8,0 | 1,0 | 3,5 | Trasparente / Transparent          | -         | 1.000   |
| 14939CA00 | 19,5 | 2,5 | 5,0 | 6,2 | 8,0 | 1,0 | 3,5 | Trasparente / Transparent          | -         | 1.000   |
| 14940CA08 | 16,0 | 3,0 | 5,0 | 2,0 | 8,0 | 1,0 | 3,5 | Blu trasparente / Transparent blue | V0 (UL94) | 1.000   |
| 14941CA08 | 16,0 | 3,0 | 5,0 | 2,5 | 8,0 | 1,0 | 3,5 | Blu trasparente / Transparent blue | V0 (UL94) | 1.000   |
| 14942CA08 | 15,5 | 3,5 | 5,0 | 3,0 | 8,0 | 1,0 | 3,5 | Blu trasparente / Transparent blue | V0 (UL94) | 1.000   |
| 14943CA08 | 15,5 | 3,5 | 5,0 | 3,0 | 8,0 | 1,0 | 3,5 | Blu trasparente / Transparent blue | V0 (UL94) | 1.000   |
| 14944CA08 | 16,0 | 3,0 | 5,0 | 3,5 | 8,0 | 1,0 | 3,5 | Blu trasparente / Transparent blue | V0 (UL94) | 1.000   |
| 14945CA08 | 17,5 | 2,5 | 5,0 | 3,8 | 8,0 | 1,0 | 3,5 | Blu trasparente / Transparent blue | V0 (UL94) | 1.000   |
| 14946CA08 | 16,5 | 3,0 | 5,0 | 4,0 | 8,0 | 1,0 | 3,5 | Blu trasparente / Transparent blue | V0 (UL94) | 1.000   |
| 14947CA08 | 17,5 | 2,5 | 5,0 | 4,8 | 8,0 | 1,0 | 3,5 | Blu trasparente / Transparent blue | V0 (UL94) | 1.000   |
| 14948CA08 | 19,5 | 2,5 | 5,0 | 6,0 | 8,0 | 1,0 | 3,5 | Blu trasparente / Transparent blue | V0 (UL94) | 1.000   |