

# SEPARADOR CILÍNDRICO ANTI-LOST



## Descripción Técnica


**Material:** PA6 + 25% FV

**Autoextinguibilidad:** UL94-HB

**Color:** Negro

**Temperatura de trabajo:** -35°C ~ +110°C

Todas las medidas están indicadas en mm



| Codigo        | A   | B     | C     | D     | E   | Conf./piezas |
|---------------|-----|-------|-------|-------|-----|--------------|
| 10079BB0102.0 | 2,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0103.0 | 3,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0104.0 | 4,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0105.0 | 5,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0106.0 | 6,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |

| Codigo        | A    | B     | C     | D     | E   | Conf./piezas |
|---------------|------|-------|-------|-------|-----|--------------|
| 10079BB0107.0 | 7,0  | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0108.0 | 8,0  | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0109.0 | 9,0  | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0110.0 | 10,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0111.0 | 11,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0112.0 | 12,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0113.0 | 13,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0114.0 | 14,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0115.0 | 15,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0116.0 | 16,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0117.0 | 17,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0118.0 | 18,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0119.0 | 19,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0120.0 | 20,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0121.0 | 21,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0122.0 | 22,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0123.0 | 23,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0124.0 | 24,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0125.0 | 25,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0126.0 | 26,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0127.0 | 27,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0128.0 | 28,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0129.0 | 29,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0130.0 | 30,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0131.0 | 31,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0132.0 | 32,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0133.0 | 33,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0134.0 | 34,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0135.0 | 35,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0136.0 | 36,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0137.0 | 37,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |

| Codigo        | A    | B     | C     | D     | E   | Conf./piezas |
|---------------|------|-------|-------|-------|-----|--------------|
| 10079BB0138.0 | 38,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0139.0 | 39,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0140.0 | 40,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0141.0 | 41,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0142.0 | 42,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0143.0 | 43,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0144.0 | 44,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0145.0 | 45,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0146.0 | 46,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0147.0 | 47,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0148.0 | 48,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0149.0 | 49,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0150.0 | 50,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0151.0 | 51,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0152.0 | 52,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0153.0 | 53,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0154.0 | 54,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0155.0 | 55,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0156.0 | 56,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0157.0 | 57,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0158.0 | 58,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0159.0 | 59,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |
| 10079BB0160.0 | 60,0 | Ø 7,0 | Ø 6,2 | Ø 4,6 | 2,0 | 500          |